

# Stainless Steel Care Fluid



## Accessories:

15810001	Adapter for WSD 400,
15811002	Spray-Valve set for WSD 400,
15811400	Pressurized-Air Spray Can WSD 400,
15830001	Adjusting Valve for cans, 5 L & 10 L
15831001	Adjusting Valve for cans, 28 L
15841500	Pump-Dispenser WPS 1500, 1,5 L
15841501	Extension for WPS 1500,
15842001	Pump Dispenser,

## antistatic effect

Stainless Steel Care was specially formulated for the cleaning, protection and care of matt and polished stainless steel surfaces both indoors and outdoors and has an antistatic effect.

WEICON Stainless Steel Care removes and prevents fingerprints, removes lubricating films e.g. from fume hoods, cleans even large surfaces without leaving streaks, and provides a long-lasting protective film which repels water and prevents new dirt from clinging. The product can be used in many applications.

## Technical Data

Odour	solvent
Storage stability	24 months
Features	antistatic effect, indoors and outdoors
Colour	colourless
AOX-free*	Yes
Temperature resistance	-20 to +130 °C
Suitable for application with	WSD 400 and WPS 1500

## Storage

Keep in closed original container. Protect from direct sun light. Storage temperature may not exceed +50°C. Store container in a cool, dry and ventilated place.

## Safety and health

When using WEICON products, the physical, safety technical, toxicological and ecological data and regulations in our EC safety data sheets ([www.weicon.com](http://www.weicon.com)) must be observed.

## Available sizes:

15590001	Stainless Steel Care Fluid 1 L
15590005	Stainless Steel Care Fluid 5 L
15590010	Stainless Steel Care Fluid 10 L
15590028	Stainless Steel Care Fluid 28 L

## Note

The specifications and recommendations given in this technical data sheet must not be seen as guaranteed product characteristics. They are based on our laboratory tests and on practical experience. Since individual application conditions are beyond our knowledge, control and responsibility, this information is provided without any obligation. We do guarantee the continuously high quality of our products. However, own adequate laboratory and practical tests to find out if the product in question meets the requested properties are recommended. A claim cannot be derived from them. The user bears the only responsibility for non-appropriate or other than specified applications.

WEICON GmbH & Co. KG  
(Headquarters)  
Germany  
phone +49 (0) 251 9322 0  
info@weicon.de  
www.weicon.de

WEICON Middle East L.L.C.  
United Arab Emirates  
phone +971 4 880 25 05  
info@weicon.ae  
www.weicon.ae

WEICON Inc.  
Canada  
phone +1 877 620 8889  
info@weicon.ca  
www.weicon.ca

WEICON Kimya Sanayi Tic. Ltd. Şti.  
Turkey  
phone +90 (0) 212 465 33 65  
info@weicon.com.tr  
www.weicon.com.tr

WEICON Romania SRL  
Romania  
phone +40 (0) 3 65 730 763  
office@weicon.com  
www.weicon.com.ro

WEICON SA (Pty) Ltd  
South Africa  
phone +27 (0) 21 709 0088  
info@weicon.co.za  
www.weicon.co.za

WEICON South East Asia Pte Ltd  
Singapore  
phone (+65) 6710 7671  
info@weicon.com.sg  
www.weicon.com.sg

WEICON Czech Republic s.r.o.  
Czech Republic  
phone +42 (0) 417 533 013  
info@weicon.cz  
www.weicon.cz

WEICON Ibérica S.L.  
Spain  
phone +34 (0) 914 7997 34  
info@weicon.es  
www.weicon.es

WEICON Italia S.r.l.  
Italy  
phone (+39) 0102924871  
info@weicon.it  
www.weicon.it