

Plastic Cleaner



15204028

Plastic Cleaner 28 L

Accessories:

15810001	Adapter for WSD 400,
15811002	Spray-Valve set for WSD 400,
15811400	Pressurized-Air Spray Can WSD 400,
15830001	Adjusting Valve for cans, 5 L & 10 L
15831001	Adjusting Valve for cans, 28 L
15841500	Pump-Dispenser WPS 1500, 1,5 L
15841501	Extension for WPS 1500,
15842001	Pump Dispenser,
15843001	Pump Dispenser Special,

degreases and cleans sensitive surfaces

WEICON Plastic Cleaner cleans, degreases and evaporates without leaving residues. It can be used to clean and degrease sensitive surfaces such as plastics, rubber materials or powder-coated metal parts.

Plastic Cleaner can be used, for example, on window frames, roller blinds, plastic profiles, seals or lacquered flanges in many industrial applications.

Technical Data

Odour	almost odourless
Storage stability	24 months
Features	solvent-free, biodegradable
Colour	colourless
AOX-free*	Yes
Suitable for application with	WSD 400 and WPS 1500
IMPA-Code	551567/68/69

* AOX = Adsorbable Organic Halides (chlorine, bromine and iodine compounds)

Storage

Keep in closed original container. Protect from direct sun light. Storage temperature may not exceed +50°C. Store container in a cool, dry and ventilated place.

Safety and health

When using WEICON products, the physical, safety technical, toxicological and ecological data and regulations in our EC safety data sheets (www.weicon.com) must be observed.

Available sizes:

15204001	Plastic Cleaner 1 L
15204005	Plastic Cleaner 5 L
15204010	Plastic Cleaner 10 L

Note

The specifications and recommendations given in this technical data sheet must not be seen as guaranteed product characteristics. They are based on our laboratory tests and on practical experience. Since individual application conditions are beyond our knowledge, control and responsibility, this information is provided without any obligation. We do guarantee the continuously high quality of our products. However, own adequate laboratory and practical tests to find out if the product in question meets the requested properties are recommended. A claim cannot be derived from them. The user bears the only responsibility for non-appropriate or other than specified applications.

WEICON GmbH & Co. KG
(Headquarters)
Germany
phone +49 (0) 251 9322 0
info@weicon.de
www.weicon.de

WEICON Middle East L.L.C.
United Arab Emirates
phone +971 4 880 25 05
info@weicon.ae
www.weicon.ae

WEICON Inc.
Canada
phone +1 877 620 8889
info@weicon.ca
www.weicon.ca

WEICON Kimya Sanayi Tic. Ltd. Şti.
Turkey
phone +90 (0) 212 465 33 65
info@weicon.com.tr
www.weicon.com.tr

WEICON Romania SRL
Romania
phone +40 (0) 3 65 730 763
office@weicon.com
www.weicon.com.ro

WEICON SA (Pty) Ltd
South Africa
phone +27 (0) 21 709 0088
info@weicon.co.za
www.weicon.co.za

WEICON South East Asia Pte Ltd
Singapore
phone +65 6710 7671
info@weicon.com.sg
www.weicon.com.sg

WEICON Czech Republic s.r.o.
Czech Republic
phone +42 (0) 417 533 013
info@weicon.cz
www.weicon.cz

WEICON Ibérica S.L.
Spain
phone +34 (0) 914 7997 34
info@weicon.es
www.weicon.es

WEICON Italia S.r.l.
Italy
phone (+39) 0102924871
info@weicon.it
www.weicon.it